

metabo**Cordless hammer drill without battery, Type: SB18LTBL****Order data**

Order number	070122 SB18LTBL
GTIN	4007430302359
Item class	03D

Description**Version:****Cordless hammer drill / driver with brushless motor and two-speed gearbox.**

Choose between a complete set with 2 battery packs, charger and sturdy plastic case, or the machine without accessories in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

All battery packs from Metabo come with a 3-year warranty, irrespective of the number of charge cycles.

Further highlights such as the bright LED work light and the handy belt hook ensure even greater convenience when working. All LT and LTX models are equipped with a high-performance impact mechanism for maximum drilling performance in stone and masonry. The LTX class pulse mode helps effectively with stuck screws or when spot drilling on smooth surfaces.

To handle the most demanding applications we recommend the use of brushless types, which you can immediately identify by the "BL" in the designation. They also have thermal overload protection, which protects the motor against overheating.

- **Cordless hammer drill with optimum performance for demanding applications.**
- **High-performance impact mechanism for best work results.**
- **Integrated work light for illuminating the work area.**
- **With handy belt hook and bit holder, can be fixed either on the left or right.**

- **Numerous brands, one battery system: This product can be combined with all 18V battery packs and chargers of the CAS brands.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

Supplied with quick-change chuck; without rechargeable battery, charger and transport case.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Weight without battery	1.2 kg
Battery voltage	18 V
maximum twist drill size Ø in concrete	13 mm
Packaging	Metabox
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Type CAS 18 V
No load speed	0 - 600
No load speed	0 - 2100
Motor design	brushless
typical application	Strong
Manufacturer's designation	SB 18 LT BL
Quick-clamping chuck range	1.5 mm
Number of rechargeable batteries contained	0
maximum torque hard	75 Nm
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	38 mm
Power supply	Rechargeable battery-powered
maximum torque soft	34 Nm
maximum hammer rate	31950 min ⁻¹
Type of product	Impact drill /screwdriver

