

**metabo****Angle grinder, Type: WEV11-125****Order data**

|              |                  |
|--------------|------------------|
| Order number | 077132 WEV11-125 |
| GTIN         | 4061792176409    |
| Item class   | 03D              |

**Description****Version:****You set the limit – not your machine.**

With devices from 850 to 1,900 watts, you can find the right angle grinder for every requirement and application. Compact angle grinder with **speed control** and **the smallest grip circumference in its performance class** for perfect ergonomics.

- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked.**
- **Electronic overload protection, soft start and restart protection.**
- **Gear housing can be mounted in 90° increments for left-handed operation or for cutting.**
- **Constant speed under load.**
- **Low-fatigue like never before: Compact angle grinder with speed control and the smallest grip circumference in its performance class for perfect ergonomics.**
- **Longer service life, more power: The Metabo Marathon motor with patented dust protection, up to 20% more overload capacity and 50% more torque.**
- **Tool-free, fast disc change at the touch of a button with the Metabo M-Quick system.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Switch-off carbon brushes to protect the motor.**

**Supplied with:**

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

**Technical description**

|                            |                                |
|----------------------------|--------------------------------|
| Power supply               | Mains-powered                  |
| Connection thread          | M14                            |
| Manufacturer's designation | WEV 11-125 Quick               |
| Weight                     | 2.1 kg                         |
| Soft start                 | yes                            |
| Restart block              | yes                            |
| maximum disc Ø             | 125 mm                         |
| Cable length               | 4 m                            |
| Special features           | Quick-change system            |
| Power consumption          | 1100 W                         |
| No load speed              | 2800 - 10500 min <sup>-1</sup> |
| Type of product            | Angle grinder                  |