

metabo**Angle grinder, Type: WEV15-125****Order data**

Order number	077132 WEV15-125
GTIN	4007430243751
Item class	03D

Description**Version:****You set the limit – not your machine.**

With devices from 850 to 1,900 watts, you can find the right angle grinder for every requirement and application. Robust, **powerful angle grinder** with speed control for good work progress.

- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked.**
- **Electronic overload protection, soft start and restart protection.**
- **Gear housing can be mounted in 90° increments for left-handed operation or for cutting.**
- **Constant speed under load.**
- **Highest service life in extreme applications: Robust, powerful angle grinder with speed control and the highest power density in its class for good work progress.**
- **Longer service life, more power: The Metabo Marathon motor with patented dust protection, up to 20% more overload capacity and 50% more torque.**
- **Tool-free, fast disc change at the touch of a button with the Metabo M-Quick system.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Low-vibration additional handle Metabo VibraTech (MVT).**
- **Switch-off carbon brushes to protect the motor.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

Technical description

Weight	2.5 kg
Special features	Quick-change system
Connection thread	M14
Restart block	yes
Manufacturer's designation	WEV 15-125 Quick
Cable length	4 m
Soft start	yes
maximum disc Ø	125 mm
Power consumption	1550 W
Power supply	Mains-powered
No load speed	2800 - 11000 min ⁻¹
Type of product	Angle grinder