

metabo**Cordless hammer drill without battery, Type: SB18LTXBLI****Order data**

Order number	070122 SB18LTXBLI
GTIN	4061792188174
Item class	03D

Description**Version:****Cordless hammer drill / driver with brushless motor and two-speed gearbox.**

Choose between a complete set with 2 battery packs, charger and sturdy plastic case, or the machine without accessories in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

All battery packs from Metabo come with a 3-year warranty, irrespective of the number of charge cycles.

Further highlights such as the bright LED work light and the handy belt hook ensure even greater convenience when working. All LT and LTX models are equipped with a high-performance impact mechanism for maximum drilling performance in stone and masonry. The LTX class pulse mode helps effectively with stuck screws or when spot drilling on smooth surfaces.

To handle the most demanding applications we recommend the use of brushless types, which you can immediately identify by the "BL" in the designation. They also have thermal overload protection, which protects the motor against overheating.

- **Cordless hammer drill offering maximum power for the most demanding applications.**
- **Selectable pulse mode for unscrewing jammed screws and spot drilling on smooth surfaces.**
- **Precision Stop: more precise electronic torque coupling for exact, sensitive working.**

- **Electronic safety shut-off function: no kick-back when the drill is blocked, providing excellent protection for the operator.**
- **Integral LED work light with afterglow function for optimal brightness in the working area.**
- **With handy belt hook and bit holder, can be fixed either on the left or right.**
- **Numerous brands, one battery system: This product can be combined with all 18V battery packs and chargers of the CAS brands.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

Supplied with quick-change chuck; without rechargeable battery, charger and transport case.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Number of rechargeable batteries contained	0
Battery voltage	18 V
Power supply	Rechargeable battery-powered
maximum torque soft	65 Nm
Weight without battery	1.8 kg
maximum twist drill size Ø in steel	13 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Manufacturer's designation	SB 18 LTX BL I
maximum twist drill size Ø in wood	68 mm
maximum twist drill size Ø in concrete	16 mm
Type of rechargeable battery	Lithium-ion
typical application	Heavy Duty
maximum torque hard	130 Nm
Quick-clamping chuck range	1.5 - 13 mm
No load speed	0 - 550
No load speed	0 - 2000
Packaging	Metabox

Motor design	brushless
maximum hammer rate	38000 min ⁻¹
Type of product	Impact drill /screwdriver