

metabo**Cordless angle grinder with rechargeable battery, Type: WBLTX15125****Order data**

Order number	077127 WBLTX15125
GTIN	4061792229051
Item class	03D

Description**Version:**

Brushless 18 V angle grinder, extremely powerful yet very easy to use.

- **Battery pack can be rotated in 90° increments.**
- **Fast braking system and safety shut-off.**
- **M-Quick system for tool-free disc change.**
- **Brushless cordless angle grinder in a new generation: The most powerful in its class, as powerful as a 1500-watt mains device.**
- **Service-free brushless motor with maximum efficiency and maximum handling.**
- **Fast braking system for maximum user protection: Disc stops within 1.5 seconds after switching off.**
- **M-Quick system for tool-free disc changes at the touch of a button.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Battery pack can be rotated in 90° degree increments for best ergonomics in any working position.**
- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked to the lowest level on the market – for maximum user protection.**
- **Electronic overload protection, soft start and restart protection.**
- **Removable dust filter to protect the motor from coarse particles.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Includes rechargeable battery, charger and metaBOX. Includes protective hood, support flange, M-Quick clamping nut, additional handle Metabo VibraTech (MVT), dust protection filter and 2x LiHD batteries.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Manufacturer's designation	WB 18 LTX BL 15-125 Quick
Overload protection	yes
Kick-back stop	yes
Packaging	Metabox
Battery capacity	5.5 Ah
Motor design	brushless
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
maximum speed	10000 min ⁻¹
maximum vibration to EN	7.1 m/s ²
Dead man's circuit	no
Weight without battery	2 kg
Soft start	yes
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Weight	3 kg
maximum disc Ø	125 mm
Weight including rechargeable battery	3 kg
Restart block	yes
Number of rechargeable batteries contained	2
Battery voltage	18 V
Type of product	Angle grinder

Accessories

Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2