

**metabo****Angle grinder, Type: WEA17-125****Order data**

Order number	077132 WEA17-125
GTIN	4007430246073
Item class	03D

**Description****Version:****You set the limit – not your machine.**

With devices from 850 to 1,900 watts, you can find the right angle grinder for every requirement and application. 1,700 watt angle grinder with the power of a large grinder and the manageability of a small grinder for the fastest material removal.

- **Integrated auto-balancer for up to 50% less hand-arm vibrations, longer machine life and up to twice the tool life of the grinding wheels.**
- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked.**
- **Electronic overload protection, soft start and restart protection.**
- **Gear housing can be mounted in 90° increments for left-handed operation or for cutting.**
- **Constant speed under load.**
- **Longer service life, more power: The Metabo Marathon motor with patented dust protection, up to 20% more overload capacity and 50% more torque.**
- **Tool-free, fast disc change at the touch of a button with the Metabo M-Quick system.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Low-vibration additional handle Metabo VibraTech (MVT).**
- **Switch-off carbon brushes to protect the motor.**

**Supplied with:**

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

**Technical description**

Power consumption	1700 W
Weight	2.5 kg
Cable length	4 m
Special features	Quick-change system
Soft start	yes
Connection thread	M14
Power supply	Mains-powered
Restart block	yes
maximum disc Ø	125 mm
Manufacturer's designation	WEA 17-125 Quick
Kick-back stop	yes
No load speed	11000 min <sup>-1</sup>
Type of product	Angle grinder