

metabo**Metal face mill, Type: PFM17****Order data**

Order number	078162 PFM17
GTIN	4061792210349
Item class	03D

Description**Version:**

- **Fast, clean removal of welding beads in a single operation with the newly developed metal face mill.**
- **Face milling produces small metal chips (no metal dust which is hazardous to health).**
- **One-touch controller: patented, tool-free milling depth adjustment in 0.1 mm increments.**
- **Ready to use in seconds thanks to tool-free fixed magnetic guide rail (50 cm long, expandable).**
- **Simple, convenient changing of the inserts on the milling head.**
- **Slim handle area and large, tool-free adjustable bridge handle for safe, even guidance.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics with adjustment wheel: for working with material-appropriate speeds that remain constant under load.**
- **Electronic soft start and restart protection.**
- **With metaBOX, the intelligent solution for transport and storage.**

Supplied with:

- **Magnetic guide rail (50 cm long)**
- **3 universal carbide inserts**
- **Bridge handle**
- **Screwdriver for Torx screws 15**
- **4 AF screwdriver with T-handle**
- **10 AF open-ended spanner**
- **metaBOX 280 L**

Technical description

Data sheet

Increments of milling depth adjustment	0.1 mm
Restart block	yes
Output power	970 W
maximum vibration to EN	4.1 m/s ²
Sound power level (LwA)	102 dB(A)
Rated power	1700 W
No load speed	8000 - 12600 min ⁻¹
Noise pressure level	91 dB(A)
Packaging	Metabox
On/Off switch	yes
Nominal voltage	230 V
Power supply	Mains-powered
Weight	4.6 kg
Cable length	3.6 m
Soft start	yes
Type of product	Milling machine