

Garant**GARANT Master Mute cutting head, left-hand, System / insert size: DM/7****Order data**

Order number	264839 DM/7
GTIN	4067263708001
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: STFCL

suitable indexable insert: TC.. 16T3..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 32 mm

Technical description

Centre offset L_3	32 mm
ISO code cutting head	STFCL

Overall length L	27 mm
Insert screw	269028 50
Series	Master Mute
suitable indexable insert	TC.. 16T3..
System	DM
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Approach angle	93 °
Cutting point / joint	40 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head