


**TMSERROR, Type: GBH18V24C**

**Order data**

Order number	075515 GBH18V24C
GTIN	4053423235067
Item class	03B

**Description**
**Version:**

**18-V cordless hammer drill with SDS-plus tool mounting** and brushless motor.

- **Overload clutch to protect both user and machine.**
- **Reversible.**
- **Extremely sturdy: Electronic Motor Protection switches off the motor if it is overloaded. Fully operational even after a drop test from 2 m on to concrete.**

Cordless hammer drill with integrated Bluetooth connectivity module.

- **Kickback Control and Vibration Control.**
- **User interface for selecting the tool mode (Auto/Favourite).**

**Supplied with:**

Including 2× 18V / 5.0 Ah Li-ion batteries, charger, depth stop, 1/1 L-BOXX inlay for device and charger and L-BOXX.

**Note:**

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

**Technical description**

Battery voltage	18 V
Manufacturer's designation	GBH 18V-24 C

maximum vibration to EN	16 m/s <sup>2</sup>
Tool arbor shape	SDS-plus
Battery capacity	5 Ah
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	30 mm
Packaging	Modular case (L-Boxx)
maximum hammer rate	4350 min <sup>-1</sup>
Weight	2.9 kg
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Number of rechargeable batteries contained	2
maximum twist drill size Ø in concrete	24 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Impact energy	2.4 J
Type of product	Hammer drill

---

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
--	------------