

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/8
Order data

Order number	264839 DM/8
GTIN	4067263708018
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SVUCL

suitable indexable insert: VC.. 1604..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre offset L_3 : 27 mm

Technical description

Insert screw	269028 49
System	DM
ISO code cutting head	SVUCL
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Approach angle	93 °
Overall length L	32 mm
Series	Master Mute
Cutting point / joint	40 mm
suitable indexable insert	VC.. 1604..

Centre offset L ₃	27 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head