

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/5

Order data

Order number	264839 DM/5
GTIN	4067263707981
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SCLCL

suitable indexable insert: CC.. 1204..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

Insert screw	269028 49
Minimum pre-drill $\varnothing D_{\min}$	50 mm

ISO code cutting head	SCLCL
Overall length L	27 mm
suitable indexable insert	CC.. 1204..
Approach angle	95 °
System	DM
Cutting point / joint	40 mm
Centre offset L ₃	27 mm
Series	Master Mute
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head