

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/3

Order data

Order number	264839 DM/3
GTIN	4067263707967
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: PTFNL

suitable indexable insert: TN.. 1604..

Approach angle: 91 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

suitable indexable insert	TN.. 1604..
Minimum pre-drill $\varnothing D_{\min}$	50 mm

Lever screw	259018 19
Overall length L	26 mm
Lever	259015 20
Shim	269005 15
Centre offset L ₃	27 mm
System	DM
Approach angle	91 °
ISO code cutting head	PTFNL
Series	Master Mute
Cutting point / joint	40 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head