



## Torque screwdriver with scale, to take D 6.3 bits, maximum torque: 200cNm



### Order data

Order number	659956 200
GTIN	7610733291687
Item class	63D

### Description

#### Version:

**Power grip** with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

**Bit holder with magnet** to take C 6.3 bits.

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

Overall length L	144 mm
Setting the trigger value	with adjustment scale
Feedback	triggering
Torque measuring accuracy	±6 %
Weight	113 g
Adjustable trigger value	adjustable
Torque range	0.4 - 2 Nm

Data can be recorded	no
Direction of tightening	Right-hand tightening
Measurement technology	mechanical
Scale graduation, 1 graduation =	5 cNm
maximum torque	200 cNm
Connection format	Bit holder 1/4 inch
Torque range	40 - 200 cNm
Standard	DIN EN ISO 6789
Measurement process	Torque
Bit socket	D 6.3
Release signalling	acoustic
Release signalling	haptisk
Calibration	O1
Display	analogue
Test certificate	Manufacturer's test certificate
Trigger principle	mechanical short travel release
Torque fixed setting	no
Type of product	Torque screwdriver

## Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20