


**BDMT 170408 ER-JT, PR1225, Type: ST1400**

**Order data**

Order number	227537 ST1400
GTIN	4960664609475
Item class	25A

**Description**
**Note:**

Standard application values for  $a_e = 0.3 \times D$ .

Exactly 90° up to  $a_p = 9$  mm.

Corner radius: 0.8 mm

Feed  $f_z$  per tooth: 0.09 – 0.22 mm

**Technical description**

Feed $f_z$ per tooth	0.09 – 0.22 mm
Type	ST1400
Corner radius	0.8 mm
ISO code indexable insert	BDMT 170408 ER-JT
Grade	PR1225
Tool material	Carbide
Type of product	Indexable insert for milling

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 500 N/mm <sup>2</sup>	suitable	200 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	140 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	180 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	180 m/min	M
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		