



## Torque screwdriver without scale, to take interchangeable blades, maximum torque: 200cNm



### Order data

|              |               |
|--------------|---------------|
| Order number | 659958 200    |
| GTIN         | 7610733291731 |
| Item class   | 63D           |

### Description

#### Version:

**Power grip** with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque can be set by stepless adjustment using a torque analyser (No. 654300 – 654460) and a 5 AF hexagon screwdriver (not supplied). To **take 6 mm interchangeable blades** (No. 659920 – 659928).

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

|                                 |            |
|---------------------------------|------------|
| Calibration                     | O6         |
| Calibration                     | O7         |
| Torque range                    | 0.4 - 2 Nm |
| set torque                      | 100 cNm    |
| Data can be recorded            | no         |
| suitable interchangeable blades | 6 mm       |

|                           |   |
|---------------------------|---|
| Direction of tightening   | Right-hand tightening                               |
| Feedback                  | triggering  |
| Measurement process       | Torque  |
| Reversible reading        | cNm   |
| Trigger principle         | mechanical short travel release                     |
| Release signalling        | acoustic  |
| Release signalling        | haptisk   |
| Standard                  | DIN EN ISO 6789                                     |
| Overall length L          | 124 mm  |
| set torque                | 1 Nm  |
| Measurement technology    | mechanical  |
| Connection format         | exchangeable blade                                  |
| Torque range              | 40 - 200 cNm  |
| Test certificate          | Manufacturer's test certificate                     |
| Setting the trigger value | without setting scale<br>(requires torque analyser) |
| Torque measuring accuracy | ±6 %  |
| Adjustable trigger value  | preset  |
| maximum torque            | 200 cNm   |
| Torque fixed setting      | no  |
| Type of product           | Torque screwdriver                                  |

## Services

Calibration and adjustment Torque screwdriver without scale maximum torque 0,04-20 N·m

020170 0,04-20