

metabo
Cordless drill / driver without rechargeable battery with Quick System, Type: BSLBLQ

Order data

Order number	070271 BSLBLQ
GTIN	4061792122727
Item class	03D

Description
Version:
Cordless drill drivers with and without Metabo Quick System.

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Brushless drill/driver with extremely compact design for general applications.**
- **Metabo Quick-System: quick change of arbor and insert tools for flexible working.**
- **With practical belt hook and bit holder, optionally fixable on the right or left.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

With quick-change drill chuck, without battery, without charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

suitable battery - supplier / battery type / voltage	Type CAS 18 V
Number of rechargeable batteries contained	0
maximum torque hard	60 Nm
Packaging	Metabox
Quick-clamping chuck range	1.5 - 13 mm
Motor design	brushless
Battery voltage	18 V
Manufacturer's designation	BS 18 L BL Q
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in wood	32 mm
maximum twist drill size Ø in steel	13 mm
maximum torque soft	25 Nm
typical application	Medium
Power supply	Mains operated
No load speed	0 - 550 min ⁻¹
No load speed	0 - 1850 min ⁻¹
Weight including rechargeable battery	1.4 kg
Weight without battery	0.92 kg
Type of product	Drill/drivers
USP1	18V
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, without battery

Accessories

Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4