



## Torque screwdriver with scale, to take interchangeable blades, maximum torque: 1600cNm



### Order data

Order number	659957 1600
GTIN	7610733291724
Item class	63D

### Description

#### Version:

**Power grip** with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection). The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt. To **take 8 mm interchangeable blades** (No. 659870 – 659884). With pistol grip for delivering high torques.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

suitable interchangeable blades	8 mm
---------------------------------	------

Release signalling	acoustic
Release signalling	haptisk
Measurement technology	mechanical
Overall length L	126 mm
Torque range	3.2 - 16 Nm
Direction of tightening	Right-hand tightening
Calibration	O1
maximum torque	1600 cNm
Display	analogue
Connection format	exchangeable blade
Test certificate	Manufacturer's test certificate
Measurement process	Torque
Torque measuring accuracy	±6 %
Scale graduation, 1 graduation =	25 cNm
Torque range	320 - 1600 cNm
Standard	DIN EN ISO 6789
Setting the trigger value	with adjustment scale
Adjustable trigger value	adjustable
Feedback	triggering
Data can be recorded	no
Trigger principle	mechanical short travel release
Torque fixed setting	no
Type of product	Torque screwdriver

## Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
---	----------------