

metabo**Cordless drill / driver without rechargeable battery, Type: BSLTXBLI**

Order data

Order number	070261 BSLTXBLI
GTIN	4061792188136
Item class	03D

Description

Version:

Cordless drill drivers with and without Metabo Quick System.

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Selectable pulse operation for unscrewing fixed screws and spot drilling on smooth surfaces.**
- **Precision stop: electronic torque coupling with increased precision for precise and sensitive working.**
- **Brushless drill/driver offering maximum power for the most demanding applications.**
- **Overload protection to protect the motor against overheating.**
- **Electronic safety shut-off function: no kick-back when the drill is blocked, providing excellent protection for the operator.**
- **With handy belt hook and bit holder, can be fixed either on the left or right.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

With quick-clamping drill chuck, without battery, without charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Number of rechargeable batteries contained	0
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	68 mm
maximum torque hard	130 Nm
typical application	Heavy Duty
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Quick-clamping chuck range	1.5 - 13 mm
Packaging	Metabox
Power supply	Mains operated
Manufacturer's designation	BS 18 LTX BL I
Motor design	brushless
suitable battery - supplier / battery type / voltage	Type CAS 18 V
maximum torque soft	65 Nm
Weight without battery	1.7 kg
No load speed	0 - 550 min ⁻¹
No load speed	0 - 2000 min ⁻¹
Weight including rechargeable battery	2.2 kg
Type of product	Drill/drivers
USP1	18V

USP2

Brushless motor, without
rechargeable battery, quick-change
chuck clamping range 1.5-13

Accessories

Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4