



Torque screwdriver with scale, to take D 6.3 bits, maximum torque: 50cNm



Order data

Order number	659956 50
GTIN	7610733291670
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

Bit holder with magnet to take C 6.3 bits.

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Calibration	O1
Feedback	triggering
Release signalling	acoustic
Release signalling	haptisk
Display	analogue
Measurement process	Torque
maximum torque	50 cNm

Adjustable trigger value	adjustable
Trigger principle	mechanical short travel release
Data can be recorded	no
Weight	71 g
Bit socket	D 6.3
Measurement technology	mechanical
Test certificate	Manufacturer's test certificate
Torque range	0.1 - 0.5 Nm
Scale graduation, 1 graduation =	1 cNm
Torque measuring accuracy	±6 %
Overall length L	126 mm
Setting the trigger value	with adjustment scale
Direction of tightening	Right-hand tightening
Torque range	10 - 50 cNm
Standard	DIN EN ISO 6789
Connection format	Bit holder 1/4 inch
Torque fixed setting	no
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------