

metabo**Cordless drill/driver with Li-ion rechargeable battery, Type: BSLTXBLI****Order data**

Order number	070260 BSLTXBLI
GTIN	4061792187764
Item class	03D

Description**Version:****Cordless drill/driver with and without Metabo Quick system.**

The **Quick system saves a lot of time** if you frequently need to change between drilling and screwing. In just a few seconds, the drill chuck with drill can be replaced with a bit holder and a bit, without the need for any tools.

Choose between a **complete set** with 2 battery packs, charger and sturdy plastic case, or the **machine without accessories** in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately. All battery packs from Metabo come with a **3-year warranty**, irrespective of the number of charge cycles.

Further highlights such as the bright **LED work light** and the handy **belt hook** ensure even greater convenience when working.

- **Selectable pulse mode for unscrewing jammed screws and spot drilling on smooth surfaces.**
- **Precision stop: electronic torque coupling with increased precision for precise and sensitive working.**
- **Brushless cordless drill/driver with maximum power for the toughest applications.**
- **Precision stop: electronic torque coupling with increased precision for precise and sensitive working.**
- **Overload protection: protects the motor from overheating.**
- **Electronic safety shut-off: no kick-back when blocking the drill – for high user protection.**

- **Integrated LED work light with afterglow function for optimum brightness in the work area.**
- **With practical belt hook and bit holder, optionally fixable on the right or left.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Supplied with quick-change chuck, 2 pcs. rechargeable battery, charger and metaBOX.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Manufacturer's designation	BS 18 LTX BL I
maximum twist drill size Ø in steel	13 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Quick-clamping chuck range	1.5 - 13 mm
typical application	Heavy Duty
maximum twist drill size Ø in wood	68 mm
Battery capacity	4 Ah
Packaging	Metabox
maximum torque hard	130 Nm
Motor design	brushless
maximum torque soft	65 Nm
Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Number of rechargeable batteries contained	2
Weight without battery	1.7 kg
Weight including rechargeable battery	2.4 kg
No load speed	0 - 550 min ⁻¹

No load speed	0 - 2000 min ⁻¹
Type of product	Drill/drivers
USP1	18V
USP2	Quick-change chuck clamping range 1.5-13, in METABOX

Accessories

Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery charger Type ASC55	073890 ASC55