

**metabo****Drill, Type: BEV1300-2****Order data**

Order number	075070 BEV1300-2
GTIN	4007430314352
Item class	03D

**Description****Version:****The right drill for every hole diameter.**

Each drill has an optimum speed range for specific drilling diameters, as well as a spindle with hexagon socket for screwdriver bits for use even without a drill chuck.

- **Robust die-cast aluminum gear housing for optimum heat dissipation and durability.**
- **Rotating carbon brush bridge for maximum performance even in anti-clockwise rotation, e.g. for unscrewing stuck screws.**
- **Metabo S-automatic safety clutch: mechanical decoupling of the drive when the drill is blocked for safe working.**
- **Selectable pulse operation for unscrewing fixed screws and spot drilling on smooth surfaces.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Vario-Tacho-Constamatic (VTC) solid-shaft electronics for working at speeds appropriate to the material, which remain constant under load.**
- **Adjustment wheel for pre-selection of the speed.**
- **Two-speed gearbox.**
- **Metabo Marathon motor with patented dust protection for a long working life.**
- **Reversible.**
- **Spindle with hexagon socket for screwdriver bits for working without a drill chuck.**
- **Overload protection: protects the motor against overheating.**
- **Restart protection: prevents accidental start-up after power interruption.**

- **Handle with non-slip softgrip surface.**
- **Cable-saving ball sleeve for optimum freedom of movement when working.**
- **Carbon brush wear indicator.**

**Supplied with:**

Includes key chuck, chuck key and additional handle.

## Technical description

Maximum twist drill size Ø in steel 1st speed	16 mm
Power consumption	1300 W
Chuck clamping range	1.5 mm
Cable length	4 m
maximum speed 1st speed	1100 min <sup>-1</sup>
Reversible	yes
maximum twist drill size Ø in wood 1st speed	40 mm
maximum torque	16 Nm
maximum torque	44 Nm
maximum speed 2nd speed	3100 min <sup>-1</sup>
maximum twist drill size Ø in wood 2nd speed	25 mm
Power supply	Mains-powered
Manufacturer's designation	BEV 1300-2
maximum twist drill size Ø in steel 2nd speed	10 mm
Weight	2.7 kg
Clamping neck Ø	43 mm
Type of product	Drill