

KERN**Precision scales, type 572, maximum weighing range: 420g**

Order data

Order number	479521 420
GTIN	4045761356849
Item class	47D

Description

Version:

- **Robust metal casing.**
- **Simple self-explanatory user guide.**
- **Selectable mains and battery operation.**
- **Units of weight (e.g. screw weight) can be freely programmed.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces. Display selectable between pieces and weight.**
- **Formulation: separate memory for weight of the tare vessel and of the formulation ingredients (net total).**
- **KERN Universal Port (KUP): allows the connection of external KUP interface adapters, such as RS-232 or USB, for exchanging data and control commands, without installation effort.**

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

External rechargeable battery, data cable, printer, interface adapter such as RS-232, USB on request.

Technical description

Manufacturer's designation	572
Scale divisions	0.001 g
maximum weighing range	0 - 420 g
Minimum unit weight	0.01 g
Linearity	± 0.005 g
Dimensions of weighing plate	Ø 106 mm
Width	180 mm
Net weight	2.3 kg
Depth	310 mm
Power supply	Mains operated
Power supply	Mains-powered
Settling time	3 s
Height	85 mm
Reproducibility	0.002 g
Calibration	Price on request
Type of product	Precision balance