



Cordless tapper without rechargeable battery with Quick System, Type: GBLTXBLQI



Order data

Order number	070281 GBLTXBLQI
GTIN	4061792188198
Item class	03D

Description

Version:

Cordless drill drivers with and without Metabo Quick System.

The **Quick System** saves a lot of time when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

The **patented thread-cutting function** of the fully-fledged cordless drill/driver enables fast and uninterrupted drilling and cleaning of threads by automatically switching the direction of rotation.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Selectable pulse operation for unscrewing fixed screws and spot drilling on smooth surfaces.**
- **Precision stop: electronic torque coupling with increased precision for precise and sensitive working.**
- **Quick-change tapping chuck for mounting taps with square and cylindrical drill bits.**

- **Very durable and long tool life for the taps thanks to intelligent torque monitoring.**
- **Metabo Quick system: quickly change the toolholder and insertion tool for flexible working.**
- **Unique Metabo brushless motor for quick working and maximum efficiency when drilling and screwing.**
- **Selectable pulse mode for unscrewing jammed screws and spot drilling on smooth surfaces.**
- **Precision Stop: more precise electronic torque coupling for exact, sensitive working.**
- **Overload protection to protect the motor against overheating.**
- **Electronic safety shut-off function: no kick-back when the drill is blocked, providing excellent protection for the operator.**
- **With handy belt hook and bit holder, can be fixed either on the left or right.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Including quick-change tapping chuck M4-M6, M8-M12, additional handle and without rechargeable battery and charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Weight without battery	1.8 kg
Battery voltage	18 V
maximum twist drill size Ø in wood	68 mm
Number of rechargeable batteries contained	0
Manufacturer's designation	GB 18 LTX BL Q I
Weight including rechargeable battery	2.2 kg
maximum twist drill size Ø in steel	13 mm
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
maximum torque hard	130 Nm
No load speed	0 - 550 min ⁻¹

No load speed	0 - 2000 min ⁻¹
maximum torque soft	65 Nm
typical application	Heavy Duty
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Packaging	Metabox
Motor design	brushless
Type of product	Drill

Accessories

Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2