

metabo
Hammer drill UHEV2860-2

Order data

Order number	075576 UHEV2860-2
GTIN	4007430306234
Item class	03D

Description
Version:
Power packs for hammer drilling.

The hammer drill has a high-performance hammer action with a precise pneumatic impact mechanism that generates impacts with maximum impact energy with minimal pressure.

Metabo Quick: fast, tool-free chuck change.

Multi-hammer with 4 functions: **hammer drilling, drilling in two gears and chiselling.**

- **Vario-Tacho-Constamatic (VTC) full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Safety shut-off: mechanical decoupling of the drive when the drill is blocked for safe working.**
- **Adjusting wheel for preselection of the speed and number of impacts.**
- **Two-speed gearbox: two drilling speeds for effective drilling in wood and metal.**
- **Metabo Marathon motor with dust protection for long life.**
- **High-performance impact mechanism precision-mounted in an aluminum alloy housing: durable and robust.**
- **Perfect ergonomics thanks to the close-to-the-hand centre of gravity and optimised grip contour.**
- **Low-mounted switch protected against damage and dust.**
- **Restart protection: prevents unintentional start-up after power interruption.**
- **Locking switch for comfortable working in continuous use.**
- **Cable-friendly ball grommet for optimum freedom of movement when working.**

Supplied with:

With additional handle and depth stop. Including hammer chuck and quick-clamping drill chuck.

Technical description

Power supply	Mains-powered
Impact energy	3.4 J
Power consumption	1100 W
maximum twist drill size Ø in concrete	28 mm
Cable length	4 m
Manufacturer's designation	UHEV 2860-2 Quick
Tool arbor shape	SDS Plus
maximum twist drill size Ø in wood	35 mm
maximum twist drill size Ø in wood	30 mm
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in steel	6 mm
Packaging	Metabox
maximum hammer rate	4500 min ⁻¹
Weight	3.3 kg
No load speed	0 - 900 min ⁻¹
No load speed	0 - 2100 min ⁻¹
Nominal voltage	230
Type of product	Hammer drill