

metabo**Random orbital sander, Type: SXE3125****Order data**

Order number	077333 SXE3125
GTIN	4007430271150
Item class	03D

Description**Version:**

Lightweight, handy grinder with perfect ergonomics for low vibrations when working.

- **Vario (V) electronics ensure you work at speeds that are suitable for the material.**
- **Multi-hole sanding pad for effective extraction.**
- **Handle area with non-slip softgrip surface.**
- **Robust die-cast aluminium bearing housing.**
- **Low-vibration work thanks to smooth running.**
- **Easy-to-empty textile dustbag for working without a vacuum cleaner.**
- **Suction option by connecting an all-purpose vacuum cleaner.**

Supplied with:

"multi-hole" sanding pad with hook-and-loop fastener, hexagon key, textile dust bag.

Note:

Suitable 6-hole abrasive disc, item No. 567775, 15-hole item No. 567558 and ABRANET item No. 567800.

Technical description

Power consumption	310 W
Manufacturer's designation	SXE 3125
Orbital stroke	3.0 mm
Speed of oscillation	8000 - 24000 min ⁻¹

Weight	1.5 kg
Backing pad Ø	125 mm
Power supply	Mains-powered
maximum vibration to EN	4.9 m/s ²
Type of product	Random orbital sanders