

**KERN**
**Precision scales, type PCB, maximum weighing range: 10000g**


## Order data

Order number	479511 10000
GTIN	4045761243156
Item class	47D

## Description

### Version:

- **Selectable mains and battery operation. Attention: German version! Please order a GB adapter plug No. 08 1174\_GB separately. Auto-off after 3 minutes.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Quantity counting: Reference quantities selectable 5, 10, 25, 50 pieces. Display selectable between pieces and weight.**
- **Formulation: separate memory for weight of the tare vessel and of the formulation ingredients (net total).**

KERN Universal Port (KUP): allows the connection of external KUP interface adapters, such as RS-232 or USB, for exchanging data and control commands, without installation effort.

### Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood.

### Optional extras:

Battery No. 081561 size 6LR61; internal rechargeable battery on request. Data cable, printer, interface adapter such as RS-232 or USB on request.

## Technical description

Minimum unit weight	2 g
---------------------	-----

Linearity	± 0.3 g
Settling time	3 s
Article no of the battery / rechargeable battery fitted	081561 6LR61
Height	79 mm
maximum weighing range	10000 g
Number of batteries contained	1
Width	163 mm
Dimensions of weighing plate	150×170 mm
Net weight	1.4 kg
Reproducibility	0.1 g
Depth	245 mm
Scale divisions	0.1 g
Power supply	Battery-powered
Calibration	K2
Type of product	Precision balance

## Services

DAkkS calibrationScales maximum weighing range 50	027710 50
CalibrationScales maximum weighing range 50 kg	027700 50