

metabo
Straight die grinder, Type: GE710P

Order data

Order number	077264 GE710P
GTIN	4007430212351
Item class	03D

Description
Version:

The straight die grinders from Metabo® are among the slimmest and most compact machines on the market. The powerful motors of the mains-operated and cordless straight die grinders offer maximum productivity with high precision in all applications.

- **Precise collar for stationary use.**
- **Pre-selectable speed levels.**
- **Electronic safety shutdown of the motor when the tool is blocked to ensure safe working.**

The straight grinders with a **long grinding spindle** are **ideal for deburring** or grinding weld seams in hard-to-reach places.

Supplied with:

Collet 6 mm, rubber protection cap, 1 open-ended spanner.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Power supply	Mains-powered
maximum vibration to EN	5.6 m/s ²
Speed range	10000 - 30500 min ⁻¹
maximum collet Ø	6 mm
electronic speed pre-selection	yes
Manufacturer's designation	GE 710 Plus

Weight	1.6 kg
Power consumption	710 W
Type of product	Straight die grinder