

**Cordless drill / driver without battery FlexiClick system, Type: GSR1890FCS****Order data**

Order number	070107 GSR1890FCS
GTIN	4059952617428
Item class	03B

**Description****Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Can be retrofitted with a **connectivity** module. Full flexibility: with many adjustable options, the **FlexiClick** system is the optimum solution for all working situations.

- **Suitable for effortless hammer drilling in concrete up to 10 mm Ø.**
- **Compact and powerful design with only 136 mm head length and a maximum hard torque of 64 Nm.**

**Supplied with:**

Including L-BOXX **without** battery and charger.

**Note:**

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

**Technical description**

Speed range 1st speed	0 - 630 min <sup>-1</sup>
Manufacturer's designation	GSR 18V 19 FC
Motor design	Brushless motor
typical application	Strong
maximum twist drill size Ø in steel	13 mm
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of rechargeable battery	Lithium-ion
maximum torque hard	64 Nm
Speed range 2nd speed	0 - 2100 min <sup>-1</sup>
Interface	Bluetooth interface
maximum torque soft	36 Nm
maximum twist drill size Ø in wood	68 mm
Number of rechargeable batteries contained	0
Weight	1.1 kg
Power supply	Mains operated
Quick-clamping chuck range	1.5 - 13 mm
maximum vibration to EN	<2,5 m/s <sup>2</sup>
Battery voltage	18 V
Type of product	Drill/driver

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
--	------------