



Cordless inspection camera, Manufacturer's designation: M12-360IC



Order data

Order number	492712 M12-360IC
GTIN	4058546410254
Item class	03L

Description

Version:

Compact cordless inspection camera for visual inspection of places that are difficult to access.

- **Large 4.3-inch LCD screen for sharp and clear images.**
- **Screen can be rotated by 270°.**
- **5 brightness levels ensure optimum lighting.**
- **3-step digital zoom for quick focus on specific points.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 1× 12 V / 2.0 Ah Li-ion battery, charger, camera cable, hook, magnet, mirror, carrying case.

Technical description

Length of the camera cable	1200 mm
Camera head Ø	10 mm
IP Index of Protection	IP 67

Battery capacity	2 Ah
Weight	0.9 kg
Display resolution	480×272 px
Manufacturer's designation	M12 360IC
Display size	4.3 in
Power supply	Mains operated
Battery voltage	12 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Carrying case
Type of product	Endoscope