



Cordless core drilling machine, Type: 71700361



Order data

Order number	076525 71700361
GTIN	4014586898285
Item class	03F

Description

Version:

Small single-speed magnetic core drilling machine with powerful lift and brushless EC motor. Very high functionality for mobile work around the building site.

- **For maximum performance, an 18-V AMPShare ProCore battery is recommended.**
- **Reversible.**
- **Extra-narrow permanent magnet with magnetic bias.**
- **Flexibility for all mobile drilling operations such as core drilling, twist drilling, thread tapping, countersinking and reaming.**
- **Simple and clear operating concept in the user's field of view.**

Supplied with:

AKBU 35 PMQ Select **without battery, incl.** coolant pump, lashing strap, swarf hook, centring pin, guard, drive-out drift, carrying case.

Note:

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867.

Technical description

Width of the magnetic base	70 mm
maximum speed	130 - 520 min ⁻¹
Weight	12.2 kg
maximum reamer Ø	18 mm
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Bosch 18 V
Working stroke	135 mm
maximum twist drill size Ø in steel	18 mm
Tool arbor shape	QuickIN / MT2
Length of magnetic base	195 mm
Boring depth	Core drills in steel maximum 50 mm
Battery voltage	18 V
Manufacturer's designation	AKBU 35 PMQ AS
Power supply	Mains operated
Height	450 mm
maximum countersink Ø	30 mm
Number of rechargeable batteries contained	0
maximum machine tap Ø in steel	M14
Packaging	Carrying case
Manufacturer ID	71700361
Type of product	Drill