

metabo**Burnishing machine, Type: SE17-200****Order data**

Order number	077754 SE17-200
GTIN	4007430323545
Item class	03D

Description**Version:**

High-performance burnishing machine with powerful 1700-watt motor for grinding, satin finishing, brushing and high-gloss polishing.

- **Slim grip area for optimal guidance.**
- **Metabo Marathon motor with patented dust protection to ensure a long service life.**
- **Spindle lock and tool-free clamping nut for quick accessory changes.**
- **Quick and tool-free adjustment of the guard and additional handle.**
- **Smooth-running, form-fitting mounting arbor for an even surface finish.**
- **Overload protection, soft start and restart protection.**
- **Switch-off carbon brushes to protect the motor.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics with adjustment wheel: for working with material-appropriate speeds that remain constant under load.**

Supplied with:

With additional handle.

Technical description

Power supply	Mains-powered
Weight	2.9 kg
Manufacturer's designation	SE 17-200 RT

Power consumption	1700 W
Cable length	4 m
Speed range	800 - 3000 min ⁻¹
Toolholder	M 14
Sander roller length	50 - 100 mm
Torque	17 Nm
Sander roller Ø	100 - 200 mm