

metabo
Fillet weld grinder, Type: KNSE9-150

Order data

| | |
|--------------|------------------|
| Order number | 077765 KNSE9-150 |
| GTIN | 4007430298867 |
| Item class | 03D |

Description
Version:

Very flat 950-watt fillet weld grinder for machining stainless steel fillet welds in tight spaces.

- **Double-reduction gear for efficient working.**
- **Removable protective hood, can be adjusted without using tools.**
- **Overload protection, soft start, restart protection.**
- **Switch-off carbon brushes to protect the motor.**
- **Vario-Constamatic (VC) full-wave electronics with adjustment wheel: for working with material-appropriate speeds that remain virtually constant under load.**
- **Metabo Marathon motor with patented dust protection to ensure a long service life.**
- **Sturdy planetary gear for a particularly long service life.**
- **Low-maintenance belt drive for a long service life.**

Supplied with:

Protective hood, additional handle, 1 pc. fleece compact disc (150×6×25.4 mm; medium), 1 pc. fleece compact disc (150×6×25.4 mm; very fine), 2 pcs. fleece compact discs (150×3×25.4 mm; medium), 1 pc. polishing file including 2 abrasive paper strips and sheet metal case.

Technical description

| | |
|----------------------------|------------|
| Toolholder | M 14 |
| Power consumption | 950 W |
| Manufacturer's designation | KNSE 9-150 |

| | |
|--------------|------------------------------|
| Weight | 2.7 kg |
| Power supply | Mains-powered |
| Cable length | 4 m |
| Speed range | 900 - 3800 min ⁻¹ |
| Disc Ø | 150 mm |