



Compact core drilling machine 72732361



Order data

Order number	076527 72732361
GTIN	4014586897356
Item class	03F

Description

Version:

Extremely small and light-weight single-speed compact magnetic core drilling machine with minimal dimensions for use in confined spaces in the workshop and on the building site.

- **Fixed upright drilling motor for working in confined spaces.**
- **Space-saving ratchet operation from both sides.**
- **Optimal view of the drilling site.**
- **Unique centre feed for cutting depths up to 35 mm.**

Supplied with:

Supplied with 1× 1/2 inch ratchet, 1/2 inch socket extension, coolant pump, lashing strap, swarf hook, centring pin, guard, additional handle, internal hex socket 5 mm, internal hex socket with T handle 5 mm, case.

Technical description

maximum machine tap \varnothing in steel	M12 mm
Power supply	Mains-powered
Weight	8.5 kg
Length of magnetic base	175 mm
maximum twist drill size \varnothing in steel	16 mm

Tool arbor shape	Weldon
Power consumption	1200 W
Tool arbor size	19 mm (3/4 inch)
Width of the magnetic base	80 mm
maximum countersink \varnothing	32 mm
maximum core drill \varnothing in steel	36 mm
Manufacturer's designation	KBC 36 MAGFORCE
maximum speed	130 - 520 min ⁻¹
Working stroke	46 mm
Height	169 mm
Packaging	Carrying case
Type of product	Core drilling machine