

metabo**Electronic belt file, Type: BFE9-20****Order data**

Order number	077720 BFE9-20
GTIN	4007430298829
Item class	03D

Description**Version:**

Powerful, compact belt file for grinding, burnishing and deburring in hard-to-reach places.

- **Vario-Constamatic (VC) full-wave electronics with adjustment wheel: for working with material-appropriate speeds that remain virtually constant under load.**
- **Linishing attachment can be pivoted through 270° without using tools, enabling it to adjust to any working position.**
- **Profiled drive roller: reduces slipping of the linishing belt.**
- **Linishing belt can be changed without using tools; adjustable belt guide.**
- **Electronic soft start.**
- **Metabo Marathon motor with patented dust protection to ensure a long service life.**
- **Switch-off carbon brushes to protect the motor.**

Supplied with:

Additional handle, sheet metal carrying case, linishing belt arm (6, 13, 19 mm), 10 linishing belts (6×457 mm; P60), 10 linishing belts (6×457 mm; P120), 10 linishing belts (19×457 mm; P60), 10 linishing belts (19×457 mm; P120), 4 non-woven belts.

Technical description

Manufacturer's designation	BFE 9-20
Cable length	4 m
Power supply	Mains-powered
Band length	457 mm

Weight	1.8 kg
Packaging	sheet metal case
Power consumption	950 W
maximum belt speed	9 - 20 m/s
Tape width	6 - 19 mm