

Garant
Driven tool, axial, ER32, Type: 40-ER32-IK

Order data

| | |
|--------------|-------------------|
| Order number | 319965 40-ER32-IK |
| GTIN | 4067263239888 |
| Item class | 31W |

Description
Version:

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**. Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via innovative coolant management, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

Version IK – with ceramic seal set, pressures up to 70 bar, with full dry-run capability.

Version IM – with internal clamping nut.

For use on both disc and radial turrets. Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality components, long working life.**
- **Transmission of high torques.**
- **100% inspection – every driven tool undergoes a run-in program.**
- **Through cooling: specially developed and patented seal.**

Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

Suitable for:

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

Optional extras:

Suitable inserts Varia VX No. 319802 – 319888, ER quick-change adapters No. 319761 – 319781, ER collets No. 308941 – 309878, ER clamping wrenches No. 309680 – 309745. Torque screwdriver No. 211750 size 5.7.

Note:

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: www.hoffmann.ews-tools.com**
- **IC tools (internal cooling) with dry-run capability, coolant filtering < 50 µm.**
- **Recommendation: tighten VARIA VX version with a torque tool (max. 6 Nm).**
- **For heavy-duty milling work, a variant with tapered roller bearings is recommended on request.**

Technical description

| | |
|------------------|-------------|
| b ₁ | 85 mm |
| x | 102 mm |
| maximum pressure | 70 bar |
| x ₂ | 39.4 mm |
| Cooling | internal |
| Adapter | ER32 |
| VDI size | 40 |
| Tool clamping | ER32 |
| Type of product | Driven tool |