



Straight die grinder Cordless, Type: M18FDGRB



Order data

Order number	077280 M18FDGRB
GTIN	4058546412395
Item class	03L

Description

Version:

Powerful 18 V / 5.0 Ah cordless straight grinder with brushless POWERSTATE™ motor.

- **REDLINK PLUS™ electronics with digital overload protection, for more power.**
- **REDLITHIUM-ION™ rechargeable battery with single cell monitoring.**
- **Universal holder for all standard 6 and 8 mm accessories.**
- **Very slim design for increased user comfort.**
- **Interchangeable dust grilles protect the motor and increase its service life.**
- **Spindle neck with rubber pad for extra user comfort.**
- **Safeguard against accidental restart.**

Supplied with:

Supplied with charger, 6 mm collet, 8 mm collet, open ended spanners AF 15 / AF 17, 2x dust-protection grilles, HD box.

Note:

For matching spare batteries and accessories see No. 073811ff.

See No. 540200 ff for suitable burrs.

See No. 550600 ff for suitable grinding points.

See No. 551850 ff for suitable polishing points.

Technical description

Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Weight	2 kg
maximum collet Ø	6 - 8 mm
Battery voltage	18 V
Speed range	27000 min ⁻¹
Power supply	Mains operated
maximum disc Ø	50 mm
Weight including rechargeable battery	2 kg
Number of rechargeable batteries contained	1
Battery capacity	5 Ah
Manufacturer's designation	M18 FDGRB
Packaging	Modular case (HD=Heavy Duty)
Type of product	Straight die grinder