

Garant GRIDLINE

Support cabinet, for insert size length×width: 1000X630mm**Order data**

Order number	431060 1000X630
GTIN	4067263264910
Item class	41C

Description**Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

Support cabinet, casing of sheet steel, with swing door (including storage shelf) and / or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL7035 light grey, front faces RAL 7016 anthracite.

Fitted with:

Door usable height: 345 mm

Number of shelves: 1

Number of cabinet casings with door: 1

Number of cabinet casings with drawers: 0

Note:

For vibration-absorbing machine mounts, please order 4 pcs. No. 086002 size 850.

Technical description

Height of support cabinet incl. bearing sets	770 mm
Load capacity, distributed	1000 kg
Support cabinet width	856 mm

Door usable height	345 mm
Support cabinet depth	600 mm
Support cabinet height	710 mm
Number of shelves	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment	25 mm
Hoffmann perforated panel grid interval	9x9
Cylinder lock	modular barrel
Type of product	Sub-frame