


WNMG 080408, Grade: CCX

Order data

Order number	252014 CCX
GTIN	4960664901159
Item class	25E

Description

WNMG 080408 CCX Grade: CCX

Chip breaker: PP

Cutting depth a_p : 0.2 - 1.5 mm

Feed f : 0.05 - 0.35 mm/rev.

Cutting speed v_c main application: 210 - 450 m/min

Technical description

Chip breaker	PP
Tool material	Cermet
Corner radius	0.8 mm
Cutting depth a_p	0.2 - 1.5 mm
Cutting conditions	continuous
ISO code indexable insert	WNMG 080408
Cutting speed v_c main application	210 - 450 m/min
Coating	coated

Finishing/roughing assignment	Finishing
Main application	P
Feed f	0.05 - 0.35 mm/rev.
Number of changes/inserts	6
Grade	CCX
Type of product	Indexable insert for turning