



**DC.T 070204, Grade: CCX**



## Order data

Order number	260382 CCX
GTIN	4960664911561
Item class	25E

## Description

### Technical description

Tolerance	M
Number of changes/inserts	2
Cutting depth $a_p$	0.1 - 1 mm
Chip breaker	PP
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Main application	P
Tool material	Cermet
Coating	coated
Cutting conditions	continuous
Feed $f$	0.05 - 0.3 mm/rev.

ISO code indexable insert	DCMT 070204
Grade	CCX
Cutting speed $v_c$ main application	150 - 370 m/min
Type of product	Indexable insert for turning