


**DCMT 11T308, Grade: CCX**

**Order data**

Order number	260387 CCX
GTIN	4960664911592
Item class	25E

**Description**
**Technical description**

Feed f	0.05 - 0.3 mm/rev.
Tool material	Cermet
Coating	coated
Finishing/roughing assignment	Finishing
Cutting depth $a_p$	0.1 - 1 mm
Number of changes/inserts	2
Corner radius	0.8 mm
Chip breaker	PP
Tolerance	M
ISO code indexable insert	DCMT11T308
Main application	P

Grade	CCX
Cutting conditions	continuous
Cutting speed $v_c$ main application	150 - 370 m/min
Type of product	Indexable insert for turning