


VBMT 160404, Grade: CCX

Order data

Order number	261182 CCX
GTIN	4960664912148
Item class	25E

Description

VBMT 160404 CCX Grade: CCX
 Chip breaker: PP
 Cutting depth a_p : 0.1 - 1 mm
 Feed f : 0.05 - 0.25 mm/rev.
 Cutting speed v_c main application: 140 - 300 m/min

Technical description

ISO code indexable insert	VBMT160404
Cutting speed v_c main application	140 - 300 m/min
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting conditions	continuous
Main application	P
Corner radius	0.4 mm

Feed f	0.05 - 0.25 mm/rev.
Chip breaker	PP
Coating	coated
Grade	CCX
Cutting depth a_p	0.1 - 1 mm
Tool material	Cermet
Type of product	Indexable insert for turning