


VBMT 110308, Grade: CCX

Order data

Order number	261176 CCX
GTIN	4960664912131
Item class	25E

Description

VBMT 110308 CCX Grade: CCX

Chip breaker: PP

Cutting depth a_p : 0.1 - 1 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 140 - 300 m/min

Technical description

ISO code indexable insert	VBMT110308
Tool material	Cermet
Cutting depth a_p	0.1 - 1 mm
Feed f	0.05 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	140 - 300 m/min
Number of changes/inserts	2

Corner radius	0.8 mm
Coating	coated
Main application	P
Chip breaker	PP
Grade	CCX
Cutting conditions	continuous
Type of product	Indexable insert for turning