


TNMG 160404, Grade: CA315

Order data

Order number	251582 CA315
GTIN	4960664799725
Item class	25E

Technical description

Tool material	Carbide
Corner radius	0.4 mm
Grade	CA315
Number of changes/inserts	6
Coating	coated
Chip breaker	KG
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 350 m/min
Main application	O
ISO code indexable insert	TNMG 160404
Cutting depth a_p	0.5 - 3.6 mm

Feed f	0.15 - 0.5 mm/rev.
Type of product	Indexable insert for turning