

**DC.T 11T302, Grade: PR1725****Order data**

Order number	260385 PR1725
GTIN	4960664923441
Item class	25E

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Grade	PR1725
Feed f	0.03 - 0.2 mm/rev.
Finishing/roughing assignment	Finishing
Main application	M
Number of changes/inserts	2
Cutting speed v_c main application	60 - 200 m/min
Chip breaker	MFP-SKS
Coating	coated
Tolerance	G
Corner radius	0.2 mm
Cutting speed v_c secondary application	50 - 150 m/min

Secondary application	P
Tool material	Carbide
ISO code indexable insert	DCGT 11T302
Cutting conditions	slightly interrupted
Type of product	Indexable insert for turning