


Grinding and inspection vice with quick adjustment, Jaw width A: 120mm



Order data

Order number	363240 120
GTIN	4067263239550
Item class	32K

Description

Version:

Ground Vee grooves.

All-steel, through hardened and **precision ground all round** for 4-face machining.

With quick adjustment (no spindle).

Application:

For **machining and inspection true to gauge.**

Accuracy:

Within **0.005 mm** / 100 mm.

Supplied with:

Including sturdy **case.**

Technical description

Overall length a	255 mm
Base body height G	55 mm
Jaw height C	40 mm
Weight	13.9 kg
maximum clamping range b	140 mm
Overall width B	120 mm
Jaw width A	120 mm

Type of product

Checking vice

Accessories

Spare clamping unit complete For size 120 mm

363245 120