



MultiMaster MM 300 Plus Start, Type: 72297264



Order data

Order number	077824 72297264
GTIN	4014586898094
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Thanks to the Starlock Plus tool arbor, you have access to around 100 FEIN accessories from the Starlock and Starlock Plus performance classes.

MultiTool for interior work and renovation with the basic equipment for sawing wood, metals, plasterboard and plastics.

Supplied with:

1× plastic tool case, 1× E-Cut long-life saw blade (35 mm), 1× E-Cut long-life saw blade (65 mm), 1× E-Cut universal saw blade (44 mm).

Technical description

Weight	1.4 kg
--------	--------

Manufacturer's designation	MM 300 Plus Start
Amplitude (oscillation movement)	2 × 1.6 °
Power supply	Mains-powered
Power consumption	250 W
Toolholder	Starlock, Starlock Plus
Speed of oscillation	11000 - 20000 min ⁻¹
Cable length	5 m
Packaging	Modular case (L-Boxx)
Type of product	Oscillator