

Garant
Roughing end mill HSS-Co8, TiAlN, Ø k12 DC: 14mm

Order data

| | |
|--------------|---------------|
| Order number | 192610 14 |
| GTIN | 4067263291114 |
| Item class | 11W |

Description
Version:

With relief ground knuckle profile. The wide teeth lands permit multiple re-grinding without losing the profile.

End face geometry for plunging and unequal spacing of the teeth.

Technical description

| | |
|--|----------------------------------|
| Corner chamfer width at 45° | 0.5 mm |
| Direction of infeed | horizontal, oblique and vertical |
| Feed f_z for side milling in steel < 750 N/mm ² | 0.029 mm |
| Shank Ø D_s | 12 mm |
| Shank | DIN 1835 B to h6 |
| Tolerance nominal Ø | k12 |
| Flute length L_c | 53 mm |
| Overall length L | 110 mm |
| Corner chamfer angle | 45 degrees |
| Helix angle | 30 degrees |
| No. of teeth Z | 4 |
| Cutting edge Ø D_c | 14 mm |
| Coating | TiAlN |
| Tool material | HSS Co 8 |

| | |
|---|----------------------------------|
| Standard | DIN 844 B |
| Milling profile | NR |
| Spacing of the cutters | unequal spacing |
| Cutting width a_e for milling operation | $0.15 \times D$ for side milling |
| Through-coolant | no |
| Colour ring | without |
| Type of product | End / face mill |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|-----------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 100 m/min | N |
| Steel < 500 N/mm ² | suitable | 60 m/min | P |
| Steel < 750 N/mm ² | suitable | 45 m/min | P |
| Steel < 900 N/mm ² | suitable | 45 m/min | P |
| INOX < 900 N/mm ² | suitable | 13 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 11 m/min | M |
| GG(G) | suitable only under restricted conditions | 36 m/min | K |
| CuZn | suitable only under restricted conditions | 73 m/min | N |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | suitable only under restricted conditions | | |