

**DC.T 11T302, Grade: PDL010****Order data**

Order number	260385 PDL010
GTIN	4960664882519
Item class	25E

Technical description

ISO code indexable insert	DCGT11T302
Feed f	0.05 - 0.25 mm/rev.
Tolerance	G
Number of changes/inserts	2
Coating	coated
Corner radius	0.2 mm
Cutting speed v_c main application	100 - 400 m/min
Cutting conditions	slightly interrupted
Tool material	Carbide
Chip breaker	AP
Cutting depth a_p	0.1 - 1 mm
Finishing/roughing assignment	Finishing

Grade	PDL010
Main application	N
Type of product	Indexable insert for turning