



MaxX lifting magnet, maximum loading capacity (level): 300kg



Order data

Order number	382001 300
GTIN	
Item class	38D

Description

Version:

Compact robust design with neodymium permanent magnets. Stray magnetic flux is prevented by the "neutral crown" principle, thus preventing undesirable attraction forces acting on adjacent loads. The base body is made from a single block without any weld seams, thus ensuring constant capability. The lever has a lock which prevents accidental release of the load. Certified break-away force.

Application:

Quick and easy handling and transport of flat and round materials with 3-fold safety.

Technical description

Weight	7.5 kg
maximum \varnothing round	300 mm
Dimension D	79 mm
maximum lifting capacity round	150 kg
maximum lifting capacity flat	300 kg
minimum material wall thickness, flat	20 mm

Dimension C	79 mm
Dimension B	210 mm
Dimension G	35 mm
Dimension F	135 mm
Dimension A	165 mm
maximum length flat	1500 mm
Dimension E	63 mm
minimum material wall thickness, round	10 mm
Type of product	Lifting magnet