


**Fibre disc Actirox AF 799 (CER), Ø 180 mm, Grit: 80****Order data**

| | |
|--------------|---------------|
| Order number | 566449 80 |
| GTIN | 4018875585016 |
| Item class | 56V |

Description**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. Top type VSM Actirox AF 799 fibre discs **with very high and aggressive grinding performance**. Cool grinding and outstanding tool life.

Grit type: **100% geometrically shaped VSM ceramic grit**.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 6670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Technical description

| | |
|----------------------|-----------------|
| Grit | 80 |
| Disc Ø | 180 mm |
| Series | Actirox |
| Grinding media | Ceramic grit |
| Grinding medium code | Stainless steel |

| | |
|---|--------------------|
| Grinding media backing | Vulcanised fibre |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 180 mm |
| Bore Ø | 22.23 mm |
| optimised for material | Steel |
| optimised for material | Cast iron |
| optimised for material | Non-ferrous metals |
| maximum circumferential speed | 80 m/s |
| Type of product | Fibre disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| dry | suitable | | |